



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH363FDK

UPC:782113206554

Dimensions:

- **Height:** 9 IN
- **Length:** 25.5 IN
- **Width:** 13.25 IN

Weight:23 LB

Notes:Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 30 at 480 Vac TD 1 Ph, 40 at 600 Vac TD 1 Ph, 60 at 480 Vac TD 3 Ph, 75 at 600 Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)



- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Drawing Link](#)
- [Eaton Specification Sheet - DH363FDK](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.