# Eaton DH363FDK

# Catalog Number: DH363FDK

Eaton Heavy duty receptacle safety switch, 100 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible without neutral, Threepole, Three-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al

#### General specifications

Product Name Eaton heavy duty fusible safety switch

UPC 782113206554

Product Height

9 in

Product Weight 23 lb

Certifications

UL Listed

DH363FDK Product Length/Depth 25.5 in

Product Width 13.25 in

Catalog Number

#### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meetNEMA 3R rainproof requirements when a factory provided drain hole is opened.



# **Physical Attributes**

#### Enclosure

NEMA 12, NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision Class H

Fuse configuration Fusible without neutral

Number Of Poles Three-pole

Number of wires

3

#### Туре

Heavy duty fusible safety switch

#### Performance Ratings

Amperage Rating

100A

HP rating - max 30, 40/ 60, 75 hp (1/3PH @480, 600 V)

NEMA rating NEMA 12/3R

Voltage rating

600 V

#### Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

## Resources

Brochures Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips

Catalogs Eaton's Volume 2—Commercial Distribution

Motor Starters and Contactors — Low Voltage Catalog

Specifications and datasheets Eaton Specification Sheet - DH363FDK

Warranty guides Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia