

# Eaton DH363NRK

Catalog Number: DH363NRK

Eaton Enhanced visible blade single-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty fusible safety switch	DH363NRK
<b>UPC</b>	<b>Product Length/Depth</b>
782113206493	22.5 in
<b>Product Height</b>	<b>Product Width</b>
8.5 in	12.75 in
<b>Product Weight</b>	<b>Warranty</b>
22 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	
UL Listed	

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Class H

### Fuse configuration

Fusible with neutral

### Number Of Poles

Three-pole

### Number of wires

4

### Type

Heavy duty fusible safety switch

## Performance Ratings

### Amperage Rating

100A

### HP rating - max

30, 40/ 60, 75 hp (1/3PH @480, 600 V)

### NEMA rating

NEMA 3R

### Voltage rating

600 V

## Miscellaneous

### Product Category

Heavy Duty, Fusible with neutral

## Resources

### Brochures

[Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH363NRK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)