



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH364FDK 200A/3P HD Fusible Safety Switch 600V Nema 12

Eaton Corp

Catalog Number	DH364FDK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 200 A, Nema 12/3R, Painted Galvanized Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 50, 50/ 125, 150 HP (1/3PH @480, 600 V), #6-300 Kcmil Cu/Al
Weight per unit	55.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	200
Material	Galvanized Steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

### Dimensions and Weight

Depth	37.5
Height	11.5
Width	19

### Descriptions

Description	200A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 12
extra long description	ETN DH364FDK 200A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 200 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 50, 50/ 125, 150 hp (1/3PH @480, 600 V), #6-300 kcmil Cu/Al
Product Type	200A/3P HD Fusible Sfty SW 600V N12

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206875
Manufacturers Part Number	DH364FDK
UPC	782113206875

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	55

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	12:3R
standard	UL Listed, NEC 230.62 (C) Compliant Barrier