

Eaton DH365FGK

Catalog Number: DH365FGK

Eaton Heavy duty single-throw fused safety switch, 400 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Al



General specifications

Product Name	Catalog Number
Eaton heavy duty fusible safety switch	DH365FGK
UPC	Product Length/Depth
782113207209	45.5 in
Product Height	Product Width
10.25 in	24.38 in
Product Weight	Warranty
113 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NEC 230.62 (C) Compliant Barrier	UL Listed
Catalog Notes	
Suitable for service entrance use with a Neutral Kit installed	

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

400A

HP rating - max

250, 350 hp (3PH @480/600 V)

NEMA rating

NEMA 1

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Fusible without neutral

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - DH365FGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)