Eaton DH365FGK

Catalog Number: DH365FGK

Eaton Heavy duty single-throw fused safety switch, 400 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Al



General specifications

Product Name Eaton heavy duty fusible safety switch

UPC 782113207209

Product Height 10.25 in

Product Weight 113 lb DH365FGK Product Length/Depth 45.5 in

Product Width 24.38 in

Catalog Number

Warranty

Certifications

UL Listed

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances NEC 230.62 (C) Compliant Barrier

Catalog Notes

Suitable for service entrance use with a Neutral Kit installed



Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Туре

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating 400A

HP rating - max 250, 350 hp (3PH @480/600 V)

NEMA rating NEMA 1

Voltage rating

600 V

Miscellaneous

Product Category Heavy Duty, Fusible without neutral

Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH365FGK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia