Eaton DH365UGK

Catalog Number: DH365UGK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 400 A, NEMA 1, Painted steel, Non-Fusible, Three-pole, Three-wire, 125 at 240 Vac TD 3 Ph, 250 at 480 Vac TD 3 Ph, 350 at 600 Vac TD 3 Ph, 50 at 250 Vdc

General specifications



Catalog Number

Eaton heavy duty non-fusible safety

DH365UGK

switch

UPC

782113207223

Product Length/Depth

Product Height

12.31 in

44.31 in

Product Width

Product Weight

24.12 in

175 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications

Product or eighteen (18) months from the

UL Listed

date of shipment of the Product,

Catalog Notes

whichever occurs first.

Suitable for service entrance use with a neutral or ground lug kit installed





Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Non-fusible

Number Of Poles

Three-pole

Number of wires

3

Type

Single-throw

Performance Ratings

Amperage Rating

400A

HP rating - max

125 at 240 Vac TD 3 Ph, 250 at 480 Vac TD 3 Ph, 350 at 600 Vac TD 3 Ph, 50 at 250 Vdc

NEMA rating

NEMA 1

Voltage rating

600 V

Miscellaneous

Product Category

Heavy Duty, Non-Fusible

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH365UGK

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









Eaton.com/socialmedia

