
Eaton DH366NGK

Catalog Number: DH366NGK

Eaton Custom single-throw fused safety switch, 600 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 200, 400, 500 hp (3PH @240,480,600 V), (1)#2-(1)600 kcmil; and (1)#1/0-(1)750 kcmil Al

General specifications



switch

UPC

782113207599

Product Length/Depth Product Height

58 in 12 in

Product Width Product Weight

27.5 in 120 lb

Warranty Certifications

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.





defaultTaxonomyAttributeLabel

Type

Heavy duty fusible safety switch

Amperage Rating

600A

Number Of Poles

Three-pole

Product Category

Heavy Duty, Fusible with neutral

Voltage rating

600 V

HP rating - max

200, 400, 500 hp (3PH @240,480,600 V)

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse class provision

Class H

Fuse configuration

Fusible with neutral

Number of wires

4

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH366NGK

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia