Eaton DH367FRK

Catalog Number: DH367FRK

Eaton Enhanced visible blade single-throw safety switch, 800 A, NEMA 3R, Painted galvanized steel, Class L, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil Al



General specifications

UPC

270 lb

Product Name Catalog Number DH367FRK Eaton heavy duty fusible safety switch Product Length/Depth 782113589732 57.5 in **Product Height** Product Width 12.38 in 27.5 in **Product Weight** Warranty Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. Certifications **Catalog Notes** UL Listed Suitable for service entrance use with a

Neutral Kit installed



Physical Attributes

Enclosure

NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision

Class L

Fuse configuration Fusible without neutral

Number Of Poles Three-pole

Number of wires

3

Туре

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating 800A

HP rating - max 500, 500 hp (3PH @480/600 V)

NEMA rating NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category Heavy Duty, Fusible without neutral

Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH367FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia