

# Eaton DH367NRK

Catalog Number: DH367NRK

Eaton Heavy duty single-throw fused safety switch, 800 A, NEMA 3R, Painted galvanized steel, Class L, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 500, 500 hp (3PH @480/600 V), (4)#1/0-(4)750 kcmil Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty fusible safety switch	DH367NRK
<b>UPC</b>	<b>Product Length/Depth</b>
782113639277	57.5 in
<b>Product Height</b>	<b>Product Width</b>
12.38 in	27.5 in
<b>Product Weight</b>	<b>Warranty</b>
210 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
NEC 230.62 (C) Compliant Barrier	UL Listed

## Physical Attributes

### Enclosure

NEMA 3R

### Enclosure material

Painted galvanized steel

### Fuse class provision

Class L

### Fuse configuration

Fusible with neutral

### Number Of Poles

Three-pole

### Number of wires

4

### Type

Heavy duty fusible safety switch

## Performance Ratings

### Amperage Rating

800A

### HP rating - max

500, 500 hp (3PH @480/600 V)

### NEMA rating

NEMA 3R

### Voltage rating

600 V

## Miscellaneous

### Product Category

Heavy Duty, Fusible with neutral

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - DH367NRK](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)