# Eaton DH367URK

## Catalog Number: DH367URK

Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 800A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 500 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph

#### General specifications



Catalog Number

Eaton heavy duty non-fusible safety

DH367URK

switch

UPC

782113589756

Product Length/Depth

**Product Height** 

14.07 in

55.82 in

**Product Width** 

Product Weight

26.37 in

175 lb

Warranty

Compliances

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier

from the date of installation of the

Certifications

Product or eighteen (18) months from the date of shipment of the Product,

UL Listed

whichever occurs first.

Catalog Notes

Suitable for service entrance use with a neutral or ground lug kit installed





### **Physical Attributes**

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse configuration

Non-fusible

**Number Of Poles** 

Three-pole

Number of wires

3

Type

Single-throw

#### Performance Ratings

**Amperage Rating** 

800A

HP rating - max

500 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph

NEMA rating

NEMA 3R

Voltage rating

600 V

#### Miscellaneous

**Product Category** 

Heavy Duty, Non-Fusible

#### Resources

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH367URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia