

Eaton DI06P-W

Catalog Number: DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386



General specifications

Product Name	Catalog Number
Eaton decorator dimmer	DI06P-W
UPC	Product Length/Depth
032664662386	2 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.001 lb	NOM
	cULus Listed

defaultTaxonomyAttributeLabel

Frequency rating

60 Hz

Special features

Preset feature

Type

Dimmer

Voltage rating

120 V

Power consumption

600 W

Wiring method

Back and side

Environmental conditions

Indoor

Switch type

Single-pole, three-way

Load type

INC

MLV

HAL

Housing

Polycarbonate

Torque rating

14 lbf-inch

Material

Polycarbonate

Actuator

Slide

Color

White

Connection type

Wire lead

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Installation videos

[How to install Eaton's universal slide dimmers](#)

Specifications and datasheets

[Eaton Specification Sheet - DI06P-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)