

# Specifications



## Eaton DI06P-W

Eaton decorator dimmer, Preset feature, #14 - 12 AWG, 120V, Bck and sd wiring, Slide actuator, Wire lead connect, Wht, Indoor, 60 Hz, incand, halo, MLV, 1-pole, 3-way, Polycarb housing, 600W 662386

### General specifications

<b>PRODUCT NAME</b>	Eaton decorator dimmer
<b>CATALOG NUMBER</b>	DI06P-W
<b>UPC</b>	032664662386
<b>PRODUCT LENGTH/DEPTH</b>	2 in
<b>PRODUCT HEIGHT</b>	4.25 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>CERTIFICATIONS</b>	NOM cULus Listed

Product specifications	
FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Preset feature
TYPE	Dimmer
VOLTAGE RATING	120 V
POWER CONSUMPTION	600 W
WIRING METHOD	Back and side
ENVIRONMENTAL CONDITIONS	Indoor
SWITCH TYPE	Single-pole, three-way
LOAD TYPE	INC MLV HAL
HOUSING	Polycarbonate
TORQUE RATING	14 lbf-inch
MATERIAL	Polycarbonate
ACTUATOR	Slide
COLOR	White
CONNECTION TYPE	Wire lead

Resources	
BROCHURES	<a href="#">Wiring Devices Buyer's Guide</a>
INSTALLATION VIDEOS	<a href="#">How to install Eaton's universal slide dimmers</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - DI06P-W</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

Follow us on social media to get the latest product and support information.

