



## DIKIT24VBC10DB Blaze 100 Led Tape Light 24V 3500K 16.4' Spool Diode Led

|                  |  |
|------------------|--|
| Catalog Number   | DIKIT24VBC10DB   |
| Manufacturer     | Diode Led  |
| Description      | Blaze 100 Led Tape Light, 24V, 3500K, 16.4 FT. Spool With 60W Omnidrive Basics Elv |
| Weight per unit  | 1.2 (lbs/each)   |
| Product Category | Lighting   |

### Features

|          |                 |
|----------|-----------------|
| Category | Specialty Items |
|----------|-----------------|

### Material, Color, and Finish

|        |              |
|--------|--------------|
| Finish | white        |
| Style  | Transitional |

### Descriptions

|                  |  |
|------------------|--|
| Description      | BLAZE 100 LED TAPE LIGHT 24V 3500K 16.4' SPOOL                                     |
| Long Description | BLAZE 100 LED Tape Light, 24V, 3500K, 16.4 ft. Spool with 60W OMNIDRIVE BASICS ELV |
| Product Type     | Led Tape Light   |

### Manufacturer Information

|                           |                             |
|---------------------------|-----------------------------|
| Brand                     | Diode Led                   |
| GTIN                      | 0084833029202               |
| Manufacturers Part Number | DI-KIT-24V-BC10DBELV60-3500 |
| UPC                       | 84833029202                 |

### Taxonomies, Classifications, and Categories

|                      |                               |
|----------------------|-------------------------------|
| Category Description | LED SPECIALTY LAMPS & MODULES |
| Type                 | LED Tapes                     |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 1.2 |