

Eaton DK3250

Catalog Number: DK3250

Eaton Series C complete molded case circuit breaker, K-frame molded case circuit breaker, DK breaker, 250 A, Three-pole, 65 kAIC at 240V, 10 kAIC at 250 Vdc, Thermal magnetic trip



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	DK3250
	UPC
	786679044124
Product Length/Depth	Product Height
4.1 in	5.5 in
Product Width	Product Weight
5.5 in	11.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

250 A

Voltage rating

240 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

DK

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Line and load

Frame

K

Frequency rating

50 to 60 Hz

Terminal material

Aluminum

Interrupt rating

65 kAIC at 240 Vac

10 kAIC at 250 Vdc

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[MOEM MCCB Product Selection Guide](#)

[Circuit breaker motor operators product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[KD3 AutoCAD 2D Footprint \(mm\)](#)

[KD3 2D Drawing Xchange](#)

[KD3 3D Inventor](#)

[KD3 AutoCAD 2D Footprint](#)

[KD3 2D PDF](#)

[KD3 3D Model Xchange](#)

Installation instructions

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

F-Frame 310+ Molded-case circuit breakers 15-225A

Eaton Specification Sheet - DK3250

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)