

DLS

4"



5 5/8"



TECHNICAL SPECIFICATIONS:

- :: Construction: Spun aluminum
- :: LED: Unique enclosed DOB (Driver On Board) LED board enclosed in clear plastic casing for better damp location performance
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: White translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working Voltage: 120V AC
- :: Dimmable
- :: LED: Seoul DOB (Driver On Board) Technology
- :: Power factor: 90% +
- :: Suitable for damp locations
- :: Maximum Ambient Temperature: 104°F
- :: Energy Star-rated
- :: Fit on recessed housings / Fit on standard 4" octagonal (40) or 3" octagonal (30) electrical boxes



ACCESSORIES INCLUDED



for DLS4



for DLS6

LED DISK LIGHTS—4" & 5" / 6" ROUND

| CATALOG NO. | FINISH | WATTS | COLOR TEMP | LUMENS | DIAMETER |
|-------------|----------------|-------|------------|------------|----------|
| DLS4-27K | WHITE | 9W | 2700K | 550~600LM | 4" |
| DLS4-30K | WHITE | 9W | 3000K | 550~600LM | |
| DLS4-41K | WHITE | 9W | 4000K | 550~600LM | |
| DLS4-50K | WHITE | 9W | 5000K | 550~600LM | |
| DLS6-27K | WHITE | 15W | 2700K | 950~1000LM | 5" / 6" |
| DLS6-30K | WHITE | 15W | 3000K | 950~1000LM | |
| DLS6-41K | WHITE | 15W | 4000K | 950~1000LM | |
| DLS6-50K | WHITE | 15W | 5000K | 950~1000LM | |
| DLS6-30K-BR | BRONZE | 15W | 3000K | 950~1000LM | |
| DLS6-30K-BN | BRUSHED NICKEL | 15W | 3000K | 950~1000LM | |

