

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road 78238-0000, TX Leon Valley Phone: 210-522-0146 Fax: 210-522-0732



### DMW232MV0LTGEB10 Wet Location Flourescent 2LMP 32W Lithonia Lighting - Acuity

Catalog Number	DMW232MV0LTGEB10
Manufacturer	Lithonia Lighting - Acuity
Description	The Lithonia Lighting® 4-Foot, 2-Light White T8 Fluorescent
	Enclosed and Gasketed Strip Light By Lithonia Lighting Is Ideal
	Where Dirt, Dust, Humidity and Moisture Are Present
Weight per unit	12.1 (lbs/each)
Product Category	Fluorescent Wet Location Light

#### **Features**

average life	40,000
Ballast Type	Electronic Ballast
Fixture Type	Linear
fixture wattage	64 W
Hardware	Yes
Housing Finish	Gloss
Lamp Type	Fluorescent
Lamp Wattage	32
Material	Fiberglass
Number of Lamps	2
pallet quantity	41
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	1
Wattage	64.00000000000000

### Material, Color, and Finish

Color	Beige	
housing color	Beige	
Housing Material		
Lens Color	WHITE	
Lens Material	Acrylic	

## **Dimensions and Weight**

Height	5.5
Length	50
Width	9.5



Mounting

standard

# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road 78238-0000, TX Leon Valley Phone: 210-522-0146 Fax: 210-522-0732

Descriptions	
Description	WET LOCATION FLOURESCENT 2LMP 32W
extra long description	LITH DMW 2 32 MVOLT GEB10IS Enclose
Long Description	The Lithonia Lighting® 4-foot, 2-light white T8 fluorescent enclosed and gasketed strip light by Lithonia Lighting is ideal where dirt, dust, humidity and moisture are present
Product Type	Linear
Manufacturer Information	
Brand	Lithonia Lighting
GTIN	00784231151099
Manufacturers Part Number	DMW 2 32 MVOLT GEB10IS
UPC	784231151099
Taxonomies, Classifications, and (	Categories
Category Description	Fluorescent Fixtures & Accessories
Туре	LINEAR
Trade Size	
aperture size	4FT
Packaging	
Carton	1
Weight	12
Weight Per each	12.1
Uses, Certifications, and Standard	ls
Application	Automotive & Parking, Education, Enclosed & Gasketed, Government, Healthcare, Hospitality, House of Worship, Manufacturing, Offices & Banks, Power & Gas, Retail, Special Applications, Sports and Recreation, Transportation, Warehouses
environmental conditions	Demanding,Indoor

Surface, Suspended

CSA,UL