Eaton DNBA2020

Catalog Number: DNBA2020

Eaton BAB thermal magnetic circuit breaker, Thermal magnetic circuit breakers, 20A, 10 kAIC, Two-pole, #14-4 AWG, DNBA

General specifications



Product Name

Eaton BAB thermal magnetic circuit

breaker

UPC

782114304709

Product Height

Catalog Number

DNBA2020

Product Length/Depth

3.5 in

3.25 in

Product Width

0.4 in

Product Weight

1 lb

Certifications

CSA Certified



Physical Attributes

Number of poles

Two-pole

Type

Thermal magnetic circuit breakers

Wire size

#14-4 AWG

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

Circuit Breakers Explained

Specifications and datasheets

Eaton Specification Sheet - DNBA2020



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia