

Eaton DS262R

Catalog Number: DS262R

Eaton Type DS disconnect switch, Panel Mounted Disconnects, Type DS - Disconnect Switch, 60A, 600 Vac, 250 Vdc, Three-pole, Three-wire, Fusible, Complete unit, Class R fuses, 60A at 600 Vac fuse clips, 60A switch rating, NEC 600 type volts



General specifications

Product Name	Catalog Number
Eaton Type DS disconnect switch	DS262R
UPC	Product Length/Depth
786679047491	9.8 in
Product Height	Product Width
5.3 in	5.9 in
Product Weight	Certifications
3.3 lb	UL Listed
	CSA Certified

Catalog Notes

Terminals are suitable for either copper or aluminum cable. Suitable for Class J fuses. UL listed for use with Class R fuses when fuse clip conversion kits are used.

defaultTaxonomyAttributeLabel

Resources

Amperage Rating

60A

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Single-phase disconnect and bypass switches](#)

Specifications and datasheets

[Eaton Specification Sheet - DS262R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)