



## DSH34 3/4" Hydraulic Draw Stud

*Greenlee Textron*

Catalog Number	DSH34
Manufacturer	Greenlee Textron
Description	Easy Threading - "Dog Point" Tip Helps Eliminate Cross-Threading. Hex Key Access For Easy Removal From Tool. Laser Markings For Quick Part Identification. Use With Greenlee Battery-Hydraulic Knockout Drivers or 746A Ram. Use With Greenlee Punches and Dies. Made In The Usa. Replaces 2113B
Weight per unit	0.7100 (lbs/each)
Product Category	Hand Tool Bits, Parts, Acessor

### Features

Material	See punch and knockout driver specifications.
----------	---

### Dimensions and Weight

Size	3/4"
Thickness	See punch specifications.

### Descriptions

Description	3/4" HYDRAULIC DRAW STUD
extra long description	GRN DSH-3/4 DRAW STUD, HYD, 3/4"
Long Description	Easy threading - "dog point" tip helps eliminate cross-threading. Hex key access for easy removal from tool. Laser markings for quick part identification. Use with Greenlee battery-hydraulic knockout drivers or 746A ram. Use with Greenlee punches and dies. Made in the USA. Replaces 2113B
Product Type	Draw Stud, Hyd, 3/4"
Special Features	Easy threading - "dog point" tip helps eliminate cross-threading. Hex key access for easy removal from tool. Laser markings for quick part identification. Use with Greenlee battery-hydraulic knockout drivers or 746A ram. Use with Greenlee punches and dies. Made in the USA. Replaces 2113B

### Manufacturer Information

Brand	GREENLEE
GTIN	00783310090663
Manufacturers Part Number	DSH-3/4
UPC	783310090663

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Draw Stud



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.71

## Uses, Certifications, and Standards

Application	For 3/4" - 2" conduit size Slug-Buster® and Standard Round knockouts. Use with Greenlee battery-hydraulic knockout drivers or 746A ram.
Capacity	See punch and knockout driver specifications.