

# Eaton DT224UGK-FB

Catalog Number: DT224UGK-FB

Eaton Heavy duty double-throw non-fused safety switch, 200 A, NEMA 1, Painted steel, Non-fusible, Two-pole, Two-wire, Fiberbond, 240 Vac, 250 Vdc



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy duty double-throw non-fused safety switch	DT224UGK-FB
	UPC
	782114137291
<b>Product Length/Depth</b>	<b>Product Height</b>
11.26 in	37.69 in
<b>Product Width</b>	<b>Product Weight</b>
19.15 in	85 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Type

Heavy Duty, Double-Throw

## Amperage Rating

200A

## Number Of Poles

Two-pole

## Voltage rating

240 Vac, 250 Vdc

## Enclosure

NEMA 1

## Enclosure material

Painted steel

## Fuse configuration

Non-fusible

## Number of wires

2

## Series

Fiberbond

## Brochures

[Safety Switches Renewal Parts](#)

## Catalogs

[Switching devices catalog](#)

## Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

## Specifications and datasheets

[Eaton Specification Sheet - DT224UGK-FB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)