



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5150 N. Hwy 81  
73533-0000, OK Duncan  
Phone: 580-252-2582  
Fax: 580-252-2738



## DT305 Dual Tech Occ Sensor 24VDC Center Mount 360 40 KHZ *Wattstopper*

Catalog Number	DT305
Manufacturer	Wattstopper
Description	Combines The Benefits Of Passive Infrared (Pir) and Ultrasonic Technologies to Detect Occupancy.
Weight per unit	0.3600 (lbs/each)
Product Category	Lighting Occupancy Sensors

### Features

body	Plastic
Connection Type	Wired
included	Sensor Mask
indicator	LED Light
indoor/outdoor	Indoor
Input Voltage	18 to 28 VDC/VAC
Mounting Type	Ceiling Tile, 4 in Octagonal J-Box, Surface
Number of Connections	1.0
sensing range	1000 sq ft
Sensor Type	Occupancy
supply voltage	24 VDC/VAC
Switch Type	Motion Sensor
Voltage	24.0 V
Wire Size	#14 - #10 Awg

### Descriptions

Description	DUAL TECH OCC SENSOR 24VDC CENTER MOUNT 360 40 KHZ
extra long description	P&S DT305 DT OCC SNSR24VDC, CNTRMN
Features	Motion Sensor
Long Description	Combines the benefits of passive infrared (PIR) and ultrasonic technologies to detect occupancy.
Product Type	DT Occ SNSR24VDC, CNTRMNT 360, 40 KHZ
Special Features	Dual Technology

### Manufacturer Information

Brand	Legrand-Wattstopper
GTIN	00754182913831
Manufacturers Part Number	DT305
UPC	754182913831

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SWITCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5150 N. Hwy 81  
73533-0000, OK Duncan  
Phone: 580-252-2582  
Fax: 580-252-2738

## Trade Size

Amperage ..... 35.0

## Packaging

Carton ..... 1

Weight Per each ..... 0.36

## Uses, Certifications, and Standards

Application ..... Classrooms, Open Office, Large Offices, Computer Rooms

nema rating ..... WD 7-2000

standard ..... ROHS, UL, cUL