Eaton DT361URK

Catalog Number: DT361URK

Eaton Heavy duty double-throw non-fused safety switch, 30 A, NEMA 3R, Painted galvanized steel, Non-fusible, Three-pole, Three-wire, 600 Vac, 250 Vdc

General specifications

Product Name	Catalog Number
Eaton heavy duty double-throw non-	DT361URK
fused safety switch	UPC 782113426365
Product Length/Depth	Product Height
11.19 in	25.02 in
Product Width	Product Weight
11.95 in	34 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) yea	ar UL Listed
from the date of installation of the	Catalog Notes
Product or eighteen (18) months from the	The
date of shipment of the Product,	Suitable for service entrance use with a
whichever occurs first.	neutral or ground lug kit installed





defaultTaxonomyAttributeLabel

Туре

Heavy Duty, Double-Throw

Amperage Rating

30A

Number Of Poles

Three-pole

Voltage rating 600 Vac, 250 Vdc

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

Resources

Brochures Double-throw safety switch Expanded double-throw safety switch line Catalogs Eaton's Volume 2—Commercial Distribution Switching devices catalog Multimedia Switching Devices Flex Center **ARMS Enclosed Circuit Breaker**

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DT361URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights property of their respective Reserved.

Eaton is a registered trademark.

All other trademarks are

owners.

f in \mathbb{X}

Eaton.com/socialmedia