Eaton DT363FRK

Catalog Number: DT363FRK

Eaton Heavy duty double-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H fuses, Fusible without neutral, Three-pole, Three-wire, K-series, 600 V

General specifications

Product Name

Catalog Number

Eaton heavy duty double-throw safety

DT363FRK

switch

UPC

782113701011

Product Length/Depth

Product Height

11.95 in

37.02 in

Product Width

Product Weight

44 lb

11.19 in

Warranty

Certifications

from the date of installation of the

Catalog Notes

Product or eighteen (18) months from the

Eaton Selling Policy 25-000, one (1) year UL Listed

Suitable for service entrance use with a

date of shipment of the Product,

neutral or ground lug kit installed

whichever occurs first.

Photo is representative



default Taxonomy Attribute Label

Type

Heavy duty, double-throw

Amperage Rating

100A

Number Of Poles

Three-pole

Product Category

Heavy-duty safety switch

Voltage rating

600 V

Switch type 2

Heavy duty

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse class provision

Class H fuses

Fuse configuration

Fusible without neutral

Number of wires

3

Series

K-series

NEMA rating

NEMA 3R

Switch type

Double throw

Resources

Brochures

Double-throw safety switch

Expanded double-throw safety switch line

Catalogs

Eaton's Volume 2—Commercial Distribution

Switching devices catalog

Multimedia

ARMS Enclosed Circuit Breaker

Switching Devices Flex Center

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DT363FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia