Eaton DT365URK

Catalog Number: DT365URK

Eaton Heavy duty double-throw non-fused safety switch, 400 A, NEMA 3R, Painted galvanized steel, Non-fusible, Three-pole, Three-wire, 600 Vac, 250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number			
Eaton heavy duty double-throw non-	DT365URK			
fused safety switch	UPC 782113696447			
Product Length/Depth	Product Height			
12.5 in	53.8 in			
Product Width 23.08 in	Product Weight 144 lb			
Warranty	Certifications			
Eaton Selling Policy 25-000, one (1) year UL Listed				
from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product,	Catalog Notes Suitable for service entrance use with a			
whichever occurs first.	neutral or ground lug kit installed			



defaultTaxonomyAttributeLabel

_			
	~	~	

Heavy Duty, Double-Throw

Amperage Rating

400A

Number Of Poles

Three-pole

Voltage rating 600 Vac, 250 Vdc

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

3

Resources

Brochures
Double-throw safety switch
Expanded double-throw safety switch line
Catalogs
Switching devices catalog
Eaton's Volume 2—Commercial Distribution
Multimedia
Double Up on Safety

Switching Devices Flex Center ARMS Enclosed Circuit Breaker

Specifications and datasheets

Eaton Specification Sheet - DT365URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

© 2024 Eaton. All Rights Reserved. All other trademarks are owners.



Eaton.com/socialmedia