



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

DTAP51618 Drill/Tap, 5/16-18 (Pop)

Greenlee Textron

Catalog Number	DTAP51618
Manufacturer	Greenlee Textron
Description	Combination Drill/Tap Bit, HSS Material; Hex Shank Type; NC Thread Series; 18 Tpi; Hardened Process; 1/4 Inch Shank Diameter; 5/16 Inch Tap Size; Cut Material Mild Steel, Copper, Brass, Aluminum
Weight per unit	0.1000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Material	HSS
Process	HARDENED
Shank Diameter	1/4 INCH
Shank Type	HEX
Tap Size	5/16 INCH
Thread Series	UNC
TPI	51330

Descriptions

Additional Information	CUT MATERIAL MILD STEEL, COPPER, BRASS, ALUMINUM; TAP UPTO 10 GAUGE METAL; PACKAGING QUANTITY 1
Commodity Description	POWER TOOLS BITS, PARTS, ACCESSORIES
Description	DRILL/TAP, 5/16-18 (POP)
Long Description	COMBINATION DRILL/TAP BIT, HSS MATERIAL; HEX SHANK TYPE; NC THREAD SERIES; 18 TPI; HARDENED PROCESS; 1/4 INCH SHANK DIAMETER; 5/16 INCH TAP SIZE; CUT MATERIAL MILD STEEL, COPPER, BRASS, ALUMINUM
Product Type	Combination Drill/Tap Bit

Manufacturer Information

Brand	Greenlee Textron
GTIN	00783310116271
Manufacturers Part Number	DTAP5/16-18
UPC	783310116271

Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------

Packaging

Carton	1
Package	5
Weight Per each	0.1

DRILL/TAPS

Combination Drill/Tap Bits



DTAPKITM

- Complete hole drilling, tapping and deburring/countersinking in one operation with power drill saves labor and time.
- Back tapered beyond tap to prevent thread damage from over-drilling.
- Deburr/countersink also provided on bit beyond back taper.
- Made from hardened high-speed steel vs. carbon steel for longer life.
- High quality hex shank to ensure strong connection to drill chuck.
- Designed to tap up to 10-gauge metal.
- Quick change adaptor included in both metric and standard kits.

CAT. NO.	UPC NO.	DESCRIPTION	DTAPKIT	DTAPKITM
DTAPKITM	12151	M3-M10 6 Piece Drill/Tap Set		
DTAPKIT	17620	6-32 to 1/4-20 6-piece Drill Tap Set		
DTAP6-32	17611	6-32NC Drill/Tap Bit	X	
DTAP8-32	17612	8-32NC Drill/Tap Bit	X	
DTAP10-24	17613	10-24NC Drill/Tap Bit	X	
DTAP10-32	17614	10-32NF Drill/Tap Bit	X	
DTAP12-24	17615	12-24NC Drill/Tap Bit	X	
DTAP1/4-20	17616	1/4-20NC Drill/Tap Bit	X	
DTAP5/16-18	11627	5/16-18NC Drill/Tap Bit		
DTAP3/8-16	11628	3/8-16NC Drill/Tap Bit		
DTAPM3C	12160	M3 X .50 Drill/Tap Bit		X
DTAPM4C	12161	M4 X .70 Drill/Tap Bit		X
DTAPM5C	12162	M5 X .80 Drill/Tap Bit		X
DTAPM6C	12163	M6 X 1.00 Drill/Tap Bit		X
DTAPM8C	12164	M8 X 1.25 Drill/Tap Bit		X
DTAPM10C	12165	M10 X 1.50 Drill/Tap Bit		X

SPECIFICATIONS

Material thickness	Up to 10 gauge
Material type	Mild steel, copper, brass, aluminum
Shank	1/4" quick change hex
Drill Material	High-speed steel
Drill point	Split point with web thinning



NOTE: TO EXTEND THE LIFE OF YOUR TOOL, SEE CUTTING/THREADING OIL ON PAGE 435.

Holemaking

USA

Tel: 800.435.0786
Fax: 800.451.2632

CANADA

Tel: 800.435.0786
Fax: 800.524.2653

INTERNATIONAL

Tel: +1.815.397.7070
Fax: +1.815.397.9247