



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358



DVCL153PHIV Diva 150W Led 3WAY Ivory Clam *Lutron*

Catalog Number	DVCL153PHIV
Manufacturer	Lutron
Description	Dimmable Bulb, Wallbox Switch, 120 V, 150 W;6000 W, 60 HZ, Dimmable CFL/Led;Incandescent/Halogen Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, Ivory, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.25 LB/Ea
Weight per unit	0.2700 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Paddle Switch
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Voltage Rating	120
Wattage	600

Material, Color, and Finish

Finish	Gloss
--------	-------

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	DIVA 150W LED 3WAY IVORY CLAM
extra long description	LUT DVCL-153PH-IV DIVA CFL/LED CLAM
Special Features	Controls 150 W dimmable LED/CFL (screw-base), 600 W incandescent, or halogen loads. Paddle turns on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents.

Manufacturer Information

GTIN	00027557003308
UPC	027557003308

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole, clamshell packaging



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358

Packaging

Carton	3
Package	48
Weight Per each	0.27

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CSA, NOM