



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVCL153PWH Diva 150W Led 3WAY White *Lutron*

| | |
|------------------|---|
| Catalog Number | DVCL153PWH |
| Manufacturer | Lutron |
| Description | Dimmable Bulb, Wallbox Switch, 120 V, 150 W;6000 W, 60 HZ, Dimmable CFL/Led;Incandescent/Halogen Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.25 LB/Ea |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|----------------|---------------|
| actuator | Paddle Switch |
| connection | Wire Leads |
| insulation | Plastic |
| Material | METAL/PLASTIC |
| media | Yes |
| Poles | 1 |
| Voltage Rating | 120 |
| Wattage | 600 |

Dimensions and Weight

| | |
|------|-------------|
| Size | 4.69 x 2.94 |
|------|-------------|

Descriptions

| | |
|------------------------|---|
| Description | DIVA 150W LED 3WAY WHITE |
| extra long description | LUT DVCL-153P-WH DIVA CFL/LED BOXED |
| Special Features | Controls 150 W dimmable LED/CFL (screw-base), 600 W incandescent, or halogen loads. Paddle turns on/off. Slide up to brighten, down to dim. Provides reliable dimming of dimmable LEDs/CFLs, as well as halogens and incandescents. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00027557003056 |
| UPC | 027557003056 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Dimmer, 3-way/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.25 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | Indoor use only |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA, NOM |