Arlington

Recessed Indoor IN BOX™ for New & Retrofit Construction



DVFR1W



DVFR2W



DVFR3W



DVFR4W

included for multiple gang boxes. **FEATURES AND BENEFITS**

• Recessed box allows items, such as furniture, to be placed closer to the wall

Non-metallic, recessed electrical boxes with trim plates and wall plates. Low voltage divider

- Plugs don't extend past the wall like a regular box
- Trim plate is textured/paintable
- For power or low voltage applications
- Mounting wings hold bracket securely against wall when screws are tightened
- ‡2-hour fire rating

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	DESCRIPTION / CU. IN.	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
DVFR1W†‡	14330	Single Gang / 21.0	1	4	4.200	6.698	.750
DVFR2W*†‡	14331	2-Gang, White / 34.0	1	4	6.012	6.698	.750
DVFR3W*†	14340	3-Gang, White / 49.3	1	1	7.930	6.818	3.875
DVFR4W*†	14342	4-Gang, White / 64.5	1	1	9.742	6.818	3.875
DVFRC	14337	2-Gang, White Cover	10	10	6.012	6.698	1.017
DVFR3C	10570	Non-Metallic Blank Cover for 3-Gang Box	10	10	9.742	6.818	1.017


*Includes Voltage Separator for power and/or low voltage. †Add suffix "GC" to Catalog # when ordering in Canada to include grounding clip, for example DVFR1WGC. ‡ 2-Hour Fire Rating
















SINGLE GANG INDOOR IN BOX INCLUDES...

Recessed box, trim plate, (1) standard duplex and (1) standard GFCI face plate, (1) NM94 cable connector, (2) mounting screws, and (2) installation screws.

DVFRC can be used with the following Arlington Boxes...

- DVFR1W
- DVFR2W
- TVBS505 • TVBU505BL
- TVBU505 • TVBU505K



Screws provided for fast and easy mounting to stud



Box positioning tabs are set for 1/2" or 5/8" drywall.



Attractive! DVFR1W shown.



Optional box cover. DVFRC shown.



Scan For Video

