

Eaton E1016-1604S

Catalog Number: E1016-1604S

Eaton Crouse-Hinds series Cam-Lok J Series E1016 insulated receptacle, Up to 400A continuous, #6 AWG-250 kcmil, Green, Male, Thermoplastic elastomer (TPE), 1-1/8", Threaded stud, 600 Vac/dc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Cam-Lok J Series E1016 insulated receptacle	E1016-1604S
	UPC
	662275128386
Product Length/Depth	Product Height
3.69 in	2.25 in
Product Width	Product Weight
2.25 in	0.63 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

Product specifications

Cable size

#6 AWG-250 kcmil

Amperage Rating

Up to 400A Continuous

Voltage rating

600 Vac/dc

Material

Thermoplastic elastomer (TPE)

Type

Threaded stud

Gender

Male

Color

Green

Receptacle threaded stud size

1-1/8"

Resources

Brochures

[Cam-Lok Single Pole Plugs and Receptacles catalog](#)

Catalogs

[Cam-Lok J Series Single Pole Plugs and Receptacles catalog page](#)

Installation instructions

[EB 141 - Cam-Lok E1015 and E1016 Molded to Cable Connectors](#)

[IM 1039 - Cam-Lok E1016 and E1018 Panel Mount Receptacles](#)

[EB 9 - Cam-Lok E1016 and E1018 Connectors](#)

[IM 1004 - Cam-Lok E1016 and E1018 Double Set Screw](#)

Specifications and datasheets

[Eaton Specification Sheet - E1016-1604S](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)