


# Eaton E1016-1635S

Catalog Number: E1016-1635S

Eaton Crouse-Hinds series Cam-Lok J Series E1016 insulated receptacle, Up to 400A continuous, #6 AWG-250 kcmil, Green, Female, Thermoplastic elastomer (TPE), 1-1/8", Threaded stud, 600 Vac/dc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Cam-Lok J Series E1016 insulated receptacle	E1016-1635S
	UPC
	662275128652
Product Length/Depth	Product Height
3.69 in	2.25 in
Product Width	Product Weight
2.25 in	0.63 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

## Product specifications

### Cable size

#6 AWG-250 kcmil

### Amperage Rating

Up to 400A Continuous

### Voltage rating

600 Vac/dc

### Material

Thermoplastic elastomer (TPE)

### Type

Threaded stud

### Gender

Female

### Color

Green

### Receptacle threaded stud size

1-1/8"

## Resources

### Brochures

[Cam-Lok Single Pole Plugs and Receptacles catalog](#)

### Catalogs

[Cam-Lok J Series Single Pole Plugs and Receptacles catalog page](#)

### Installation instructions

[IM 1039 - Cam-Lok E1016 and E1018 Panel Mount Receptacles](#)

[EB 141 - Cam-Lok E1015 and E1016 Molded to Cable Connectors](#)

[IM 1004 - Cam-Lok E1016 and E1018 Double Set Screw](#)

[EB 9 - Cam-Lok E1016 and E1018 Connectors](#)

### Specifications and datasheets

[Eaton Specification Sheet - E1016-1635S](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)