

# Eaton E1049-1835ST-R

Catalog Number: E1049-1835ST-R

Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly, Up to 1135A continuous, 313-777 kcmil, Red, Female, Short throw, Rubber, Double hole bus bar, 1000 Vac/dc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly	E1049-1835ST-R
	UPC
	662275919434
Product Length/Depth	Product Height
10.25 in	4.25 in
Product Width	Product Weight
4.25 in	9.5 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

## Product specifications

### Cable size

313-777 kcmil

### Amperage Rating

Up to 1135A Continuous

### Voltage rating

1000 Vac/dc

### Gender

Female

### Color

Red

### Latch type

Short throw

### Type

Double hole bus bar

### Material

Rubber

## Resources

### Brochures

[Roughneck Single Pole High-amperage Plugs and Connectors brochure](#)

### Catalogs

[Roughneck Single Pole High Amperage Plugs and Connectors catalog page](#)

### Installation instructions

[IF 1778 - Roughneck E1049 Series Connectors and Receptacles](#)

[IF 1777 - Roughneck E1049 Series Connectors](#)

### Specifications and datasheets

[Eaton Specification Sheet - E1049-1835ST-R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)