

# Eaton E10T115AP

Catalog Number: E10T115AP

Eaton E10 toggle switch, Single-pole, ON, None, OFF, 0.563 inch lever, Spade, Single-throw, 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac, 0.47 inch bushing



## General specifications

### Product Name

Eaton E10 toggle switch

### Catalog Number

E10T115AP

### UPC

782113698007

### Product Length/Depth

1.1 in

### Product Height

2.1 in

### Product Width

0.6 in

### Product Weight

0.05 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

UL Recognized



Powering Business Worldwide

Type

Toggle Switch

Bushing length

0.47 inch bushing

Number Of Poles

Single-pole

Lever length

0.563 in

Terminals

Spade

Throw type

Single-throw

Rating

15 A at 125 Vac, 10 A at 250 Vac, 1/2 hp at 50 Vac

Series

E10

Number of positions

ON, NONE, OFF

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E10T115AP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)