

Eaton E10T215AS

Catalog Number: E10T215AS

Eaton E10 toggle switch, Two-pole, ON, None, OFF, 0.563 inch lever, Screw, Single-throw, 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac, 0.47 inch bushing



General specifications

Product Name

Eaton E10 toggle switch

Catalog Number

E10T215AS

UPC

782113698236

Product Length/Depth

0.8 in

Product Height

2.1 in

Product Width

0.7 in

Product Weight

0.07 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Recognized

CSA Certified



Powering Business Worldwide

Type

Toggle Switch

Bushing length

0.47 inch bushing

Number Of Poles

Two-pole

Lever length

0.563 in

Terminals

Screw

Throw type

Single-throw

Rating

15 A at 125 Vac, 10 A at 250 Vac, 1/2 hp at 50 Vac

Series

E10

Number of positions

ON, NONE, OFF

Catalogs[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)**Specifications and datasheets**[Eaton Specification Sheet - E10T215AS](#)**Warranty guides**[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia