

Eaton E10T215ES

Catalog Number: E10T215ES

Eaton E10 toggle switch, Two-pole, ON, None, ON, 0.563 inch lever, Screw, Double-throw, 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac, 0.47 inch bushing



Photo is representative

General specifications

Product Name

Eaton E10 toggle switch

Catalog Number

E10T215ES

UPC

782113698359

Product Length/Depth

1.3 in

Product Height

2.1 in

Product Width

0.7 in

Product Weight

0.08 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

UL Recognized



Powering Business Worldwide

Type

Toggle Switch

Bushing length

0.47 inch bushing

Number Of Poles

Two-pole

Lever length

0.563 in

Terminals

Screw

Throw type

Double-throw

Rating

15 A at 125 Vac, 10 A at 250 Vac, 1/2 hp at 50 Vac

Series

E10

Number of positions

ON, NONE, ON

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Specifications and datasheets

Eaton Specification Sheet - E10T215ES



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton E10T215ES

Catalog Number: E10T215ES

Eaton E10 toggle switch, Two-pole, ON, None, ON, 0.563 inch lever, Screw, Double-throw, 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac, 0.47 inch bushing



Photo is representative

General specifications

Product Name

Eaton E10 toggle switch

Catalog Number

E10T215ES

UPC

782113698359

Product Length/Depth

1.3 in

Product Height

2.1 in

Product Width

0.7 in

Product Weight

0.08 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

UL Recognized



Powering Business Worldwide

Type

Toggle Switch

Bushing length

0.47 inch bushing

Number Of Poles

Two-pole

Lever length

0.563 in

Terminals

Screw

Throw type

Double-throw

Rating

15 A at 125 Vac, 10 A at 250 Vac, 1/2 hp at 50 Vac

Series

E10

Number of positions

ON, NONE, ON

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Specifications and datasheets

Eaton Specification Sheet - E10T215ES



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia