



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E10T215GS Bat SW DPDT Mom 15a125v

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | E10T215GS   |
| Manufacturer     | Eaton Corp  |
| Description      | Toggle Switch, 3 Positions, 2 Poles, E10 Series, DPDT Contact Configuration, 1.3 In Overall Length, 0.7 In Overall Width, 2.2 In Overall Height, Screw Mount, 0.09 LB |
| Weight per unit  | 0.0900 (lbs/each)   |
| Product Category | Selector Switch Components  |

### Features

|            |   |
|------------|---|
| dimensions | 33.0200millimetreX17.7800millimetreX55.8800millimetre |
| Poles      | 2 in  |
| Rating     | 15A at 125 Vac, 10A at 250 Vac, 1/2 hp at 50 Vac      |

### Descriptions

|             |                         |
|-------------|-------------------------|
| Description | BAT SW DPDT MOM 15A125V |
|-------------|-------------------------|

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782113698410      |
| UPC   | 782113698410        |

### Taxonomies, Classifications, and Categories

|                      |                 |
|----------------------|-----------------|
| Category Description | TOGGLE SWITCHES |
| igcc                 | 5210            |
| Type                 | TOGGLE SWITCH   |
| unspsc code          | 39122216        |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.09 |

### Uses, Certifications, and Standards

|          |                             |
|----------|-----------------------------|
| standard | UL Recognized;CSA Certified |
|----------|-----------------------------|



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E10 Series Light Industrial Toggle Switch

E10T215GS

UPC:782113698410

### Dimensions:

- **Height:** 2.2 IN
- **Length:** 1.3 IN
- **Width:** .7 IN

**Weight:**.09 LB

**Notes:**UP and DOWN positions have momentary contacts; spring return action

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Toggle Switch
- **Bushing Length:** 0.47 inch bushing
- **Lever Length:** 0.563 inch lever
- **Number Of Poles:** Two-pole
- **Number Of Positions:** ON, OFF, ON
- **Rating:** 15A at 125 Vac, 10A at 250 Vac, 1/2 hp at 50 Vac
- **Series:** E10
- **Terminals:** Screw
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - E10T215GS](#)

### Certifications:

- UL Recognized
- CSA Certified



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.