

Eaton E22H3X10

Catalog Number: E22H3X10

Eaton E22 pushbutton, Non-metallic Assembled Indicating Light, Heavy-Duty, Standard actuator, Black, Incandescent, Resistor, NEMA 3, 3R, 4, 4X, 12, 13, 60 Vac/dc, W1226, Green, Plastic, 22.5 mm, 120 Vac/dc at 60 Hz, 110 Vac/dc at 50 Hz

General specifications



Product Name

Eaton E22 pushbutton

UPC

782113552644

Product Height

1.5 in

Product Weight

0.1 lb

Compliances

CE Marked

Catalog Number

E22H3X10

Product Length/Depth

3 in

Product Width

4 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

IEC 947-5-1 MTTA

UL 508

CSA Certified

Lloyd's Register Certified

defaultTaxonomyAttributeLabel

Type

Non-metallic Heavy-Duty

Bezel

Black

Light unit type

Incandescent, resistor

Lamp voltage

60 Vac/dc

LED lamp number

W1226

Enclosure

NEMA 4X

NEMA 3

NEMA 3R

NEMA 4

NEMA 12

NEMA 13

Series

E22

Actuator

Standard

Style

22.5 mm

Lens color

Green

Supply voltage

120 Vac/dc at 60 Hz

110 Vac/dc at 50 Hz

Lens type

Plastic

Resources

Brochures

[Pushbuttons, Indicating lights, Selector switches and Stacklights](#)

Specifications and datasheets

[Eaton Specification Sheet - E22H3X10](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)