

Eaton E22JL2N8

Catalog Number: E22JL2N8

Eaton E22 pushbutton, E22 Pushbutton, 22.5 mm, Non-Metallic Heavy-Duty, 50 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Maintained, two-position push-pull, Red actuator, Mushroom , Anodized aluminum, EMERG. STOP, No light unit

General specifications



Product Name

Eaton E22 pushbutton

UPC

782113504056

Product Height

1.5 in

Product Weight

0.08 lb

Compliances

CE Marked

Catalog Number

E22JL2N8

Product Length/Depth

2 in

Product Width

1.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 508
CSA Certified
IEC 947-5-1 MTTA
Lloyd's Register Certified

Catalog Notes

Maximum of 3 contact blocks (6 circuits) when used with supplied 3-way adapter and optional operator plug. Anodized aluminum head not suitable for ultraviolet light applications.

defaultTaxonomyAttributeLabel

Type

Push-Pull

Actuator color

Red

Bezel

Chrome

Enclosure

NEMA 4X

NEMA 4

NEMA 13

NEMA 3

NEMA 3R

NEMA 12

Actuator material

Anodized aluminum

Actuator

Mushroom

Operating mode

Push to latch

Maintained

Turn key to release

Illumination

Non-illuminated

Series

E22

Legend

EMERGENCY STOP

Light unit type

No light unit

Degree of protection

NEMA 4X

NEMA 12

NEMA 3

NEMA 3R

NEMA 4

NEMA 13

Size

Resources

Brochures

Pushbuttons, Indicating lights, Selector switches and Stacklights

Catalogs

Eaton's Volume 12—Aftermarket, Renewal Parts and Life Extension Solutions

Specifications and datasheets

Eaton Specification Sheet - E22JL2N8



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)