



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E22LED120RN 120V Ac/DC Red Led *Eaton Corp*

Catalog Number	E22LED120RN
Manufacturer	Eaton Corp
Description	Pilot Devices - Ashville Pushbutton, Led Lamp, Red, Red, Red, Continuous, 120 Vac/VDC, 22.5 MM, Led Lamp, E22, 10250T, E34 and E22 Units
Weight per unit	0.1000 (lbs/each)
Product Category	Push Button Components

Features

dimensions	0.1000 IN X 0.1000 IN X 0.1000 IN
------------	-----------------------------------

Dimensions and Weight

Size	22.5 mm
------	---------

Descriptions

Description	120V AC/DC RED LED
extra long description	ETN E22LED120RN 120V AC/DC RED LED
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to- release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Pilot Devices - Ashville Pushbutton, LED Lamp, Red, Red, Red, Continuous, 120 Vac/Vdc, 22.5 mm, LED lamp, E22, 10250T, E34 and E22 units
Product Type	120V Ac/DC Red Led
Special Features	LED

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113494050
Manufacturers Part Number	E22LED120RN
UPC	782113494050

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Pushbutton accessory

Packaging

Carton	1
Weight Per each	0.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other Stationary Machinery and Equipment Outside
Factory - Stationary Machinery and Equipment Outside Factory -
Other

standard

CSA Std. C22.2, Lloyd's Register Certified, BS 4794, IEC 337-1, UL
508, IEC 947-5-1 MTTA, CE Marked