

Eaton E34FB197LWG2A

Catalog Number: E34FB197LWG2A

Eaton E34 pushbutton, Green, Corrosion Resistant Assembled Indicating Light, Standard actuator, LED, Full voltage, NEMA 3, 3R, 3S, 4, 4X, 12, 13, 120 Vac, Bayonet base, White, Glass, 120 V

General specifications

Product Name	Catalog Number
Eaton E34 pushbutton	E34FB197LWG2A
UPC	Product Length/Depth
782114717202	.01 in
Product Height	Product Width
.01 in	.01 in
Product Weight	Warranty
.01 lb	1 year
Compliances	Certifications
FDA 3-A CE Marked	UL Listed CSA Certified

Catalog Notes

Use NEMA 4X 10250T operators where exposed to ultraviolet light



Product specifications

LED lamp number

Bayonet base

Supply voltage

120 Vac

Light unit type

LED, full voltage

Series

E34

Type

30.5 mm, Corrosion Resistant Watertight/Oiltight

Lamp voltage

120 Vac

Rating

NEMA 4X

NEMA 12

NEMA 3S

NEMA 3R

NEMA 13

NEMA 3

NEMA 4

Lens material

Glass

Lens color

White

Actuator

Standard

Resources

Brochures

10250T and E34 Class I Division 2

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - E34FB197LWG2A

Cam selection for pushbutton selectors