

Eaton E34GDB

Catalog Number: E34GDB

Eaton 30.5 mm Watertight/Oiltight Corrosion Resistant Push-Pull Unit, Class I Division 2, Standard Actuator, Plastic bus, Non-illuminated, Two-position, Maintained push and pull, E34 Series



General specifications

Product Name	Catalog Number
Eaton E34 pushbutton	E34GDB
UPC	Product Length/Depth
782113702858	1.9 in
Product Height	Product Width
2.2 in	1.9 in
Product Weight	Warranty
0.25 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
FDA 3-A	CSA Certified

Catalog Notes

Use NEMA 4X 10250T operators where exposed to ultraviolet light

Type

Class I Division 2

Operating mode

Push: maintained

Pull: maintained

Illumination

Non-illuminated

Series

E34

Number of positions

2

Rating

NEMA 12

NEMA 4X

NEMA 13

NEMA 4

NEMA 3

NEC Class I Division 2, Groups B, C and D

NEMA 3R

Size

30.5 mm

Brochures

10250T and E34 Class I Division 2

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Cam selection for pushbutton selectors

Eaton Specification Sheet - E34GDB



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia