



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E47BMS04 Limit Switch-1NO 1NC Exte *Eaton Corp*

Catalog Number	E47BMS04
Manufacturer	Eaton Corp
Description	
Weight per unit	0.5000 (lbs/each)
Product Category	Miniature & Snap Action Limit

Features

actuator	Extended straight plunger
connection	Screw Terminals
Contact Configuration	1-SPDT (Form C)
Contact Rating	15A at 250 Vac, 6A at 30 Vdc
dimensions	49.2760millimetreX17.5260millimetreX34.5440millimetre
environmental rating	NEMA 1

Descriptions

Description	LIMIT SWITCH-1NO 1NC EXTE
Product Type	Precision Limit Switch

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113770888
Manufacturers Part Number	E47BMS04
series	E47
UPC	782113770888

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
igcc	5202
unspsc code	39122213

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Automation And Logic Control Equipment
Operating Temperature	-13° to 176°F (-25° to 80°C)
standard	UL Listed:CSA Certified



Powering Business Worldwide

pe.eaton.com

Precision Limit Switch

E47BMS04

UPC:782113770888

Dimensions:

- **Height:** 1.36 IN
- **Length:** 1.94 IN
- **Width:** .69 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 250 Vac, 6A at 30 Vdc
- **Actuator:** Extended straight plunger
- **Contact Configuration:** 1-SPDT (Form C)
- **Enclosure Material:** Mineral filled phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Speed:** 0.01 mm/s-1m/s
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Series:** E47

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [E47 precision - Limit switches](#)
- [Eaton Specification Sheet - E47BMS04](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

