



Powering Business Worldwide

pe.eaton.com

## Precision Limit Switch

**E47BMS04**

**UPC:**782113770888

### Dimensions:

- **Height:** 1.36 IN
- **Length:** 1.94 IN
- **Width:** .69 IN

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 250 Vac, 6A at 30 Vdc
- **Actuator:** Extended straight plunger
- **Contact Configuration:** 1-SPDT (Form C)
- **Enclosure Material:** Mineral filled phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Speed:** 0.01 mm/s-1m/s
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Series:** E47

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [E47 precision - Limit switches](#)
- [Eaton Specification Sheet - E47BMS04](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data

