



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50BR1COMP E50 Heavy Duty Limit Switch

Eaton Corp

Catalog Number	E50BR1COMP
Manufacturer	Eaton Corp
Description	Heavy-Duty Plug-In Switch, E50 Series, Side Rotary;Momentary Spring Return Actuator, 2NO-2NC Pole Throw Configuration, 10 A @ 12 V Ac;1 A @ 125 V DC, 12 V Ac;125 V DC, Die Cast Zinc (Enclosure) Material, Screw Terminal, +10 °F Operating Temperature, +200 °F Operating Temperature, 2.46 In Overall Width, 1.54 In Overall Depth, 2.46 In Overall Height, Chemical Resistant, 1.25 LB
Weight per unit	1.3 (lbs/each)
Product Category	Heavy Duty Limit Switches

Features

actuator	Side rotary, momentary spring return
connection	Screw Terminal
Contact Configuration	2 NO-2 NC
Contact Rating	10A at 240 Vac, 1A at 250 Vdc
dimensions	4.2200 IN X 1.5400 IN X 2.4600 IN

Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH
extra long description	ETN E50BR1 E50 HEAVY DUTY LIMIT SWI

Manufacturer Information

GTIN	00782113290553
UPC	782113290553

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	1.25

Uses, Certifications, and Standards

Operating Temperature	10
standard	CSA Certified,UL Listed,RoHS Compliant