

## Eaton E50 NEMA heavy duty plug-in limit switch

E50DL1

UPC:782113290577

### Dimensions:

- **Height:** 2.46 IN
- **Length:** 1.05 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Actuator:** Side rotary low force spring return
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** -40° to 175°F
- **Series:** E50 Heavy Duty Plug In

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50DL1](#)

### Certifications:

- CSA Certified
- UL Recognized

**Product compliance:** No Data