

# Eaton E50DT3

Catalog Number: E50DT3

Eaton E50 NEMA heavy duty plug-in limit switch, Top push roller, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50



## General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50DT3
	UPC
	782113290614
Product Length/Depth	Product Height
1.88 in	1.78 in
Product Width	Product Weight
1.54 in	0.11 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
CSA Certified	
UL Recognized	

## defaultTaxonomyAttributeLabel

### Enclosure material

Die cast zinc

### Actuator

Top push roller

### Series

E50

### Operating temperature - max

201 °F

### Operating temperature - min

14 °F

### Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - E50DT3](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)