

Eaton E50 NEMA heavy duty plug-in limit switch

E50DW1

UPC:782113290669

Dimensions:

- **Height:** 1.78 IN
- **Length:** 1.85 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Actuator:** Standard duty, wobble head, spring return
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50DW1](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data