

Eaton E50KL36

Catalog Number: E50KL36

Limit Switch Lever, E50, Accessory, Clamp, Used with 0.12 (3.2) diameter rods, Stainless steel

General specifications



Product Name	Catalog Number
--------------	----------------

Eaton E50 NEMA heavy duty plug-in limit switch operator	E50KL36
---	---------

UPC

782113138282

Product Length/Depth	Product Height
----------------------	----------------

0.64 in

0.38 in

Product Width	Product Weight
---------------	----------------

1.12 in

0.15 lb

Warranty	Compliances
----------	-------------

1 year

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE



Powering Business Worldwide

Type

Accessory

Used with

Used with 0.12 (3.2) diameter rods

Actuator

Clamp

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Material

Stainless steel

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL36](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)