Eaton E50KL40

Catalog Number: E50KL40

Limit Switch Lever, E50, Accessory, Standard roller, Used with side rotary, Stainless steel

General specifications

CSA Certified

CE

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50KL40	
switch operator	UPC 782113317496
Product Length/Depth 2.1 in	Product Height 0.65 in
Product Width 0.75 in	Product Weight 0.1 lb
Warranty 1 year	Compliances RoHS Compliant
Certifications	
UL Listed	





defaultTaxonomyAttributeLabel

Туре

Accessory

Used with

Used with side rotary

Actuator

Standard roller

Series

E50

Operating temperature - max 200 °F

Operating temperature - min 10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 13, IP67

Material

Stainless steel

Resources

Catalogs Eaton's Volume 8—Sensing Solutions

Specifications and datasheets Eaton Specification Sheet - E50KL40



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights property of their respective Reserved.

Eaton is a registered trademark.

All other trademarks are

owners.

 \mathbb{X} in f •

Eaton.com/socialmedia