

## Limit Switch Lever

E50KL536

UPC:782113297910

### Dimensions:

- **Height:** .75 IN
- **Length:** 2.22 IN
- **Width:** 1.5 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Accessory
- **Actuator:** Roller on reverse side
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Material:** Nylatron
- **Operating Temperature:** 10° to 200°F
- **Series:** E50
- **Used With:** Used with side rotary

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL536](#)

**Certifications:** No Data

**Product compliance:** No Data



## Limit Switch Lever

E50KL536

UPC:782113297910

### Dimensions:

- **Height:** .75 IN
- **Length:** 2.22 IN
- **Width:** 1.5 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Accessory
- **Actuator:** Roller on reverse side
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Material:** Nylatron
- **Operating Temperature:** 10° to 200°F
- **Series:** E50
- **Used With:** Used with side rotary

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL536](#)

**Certifications:** No Data

**Product compliance:** No Data

